

Rittal – The System.

Faster – better – everywhere.



SZ 4947.000

C rails 30/15

State: 6/15/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4947.000 - C rails 30/15 to EN 60 715 for VX, TS, VX SE

Mounted directly on the horizontal enclosure profile or base configuration rail for TP, on the vertical enclosure profile using additional fastening components.



Features

Model No.	SZ 4947.000
Material	Carbon steel
Surface finish	Zinc-plated
Length	1,155 mm 45.5 "
Installation options	On the inner mounting level, on VX enclosure profile On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.808 or adapter rail for VX compatibility On the horizontal VX SE enclosure profile in the width bottom and top On the horizontal VX SE enclosure section in depth at the bottom (without mounting plate) and at the top using snap-on nut 8800.808 On the horizontal TS enclosure section In the width or depth of the 3-part AX. Depending on the installation situation, the bar will need to be shortened to the required size.
Installation options VX Base	In base/plinth width 1200 mm on the base/plinth trim panels, in conjunction with holder/spacer
installation options AX Base	In base/plinth width 1200 mm, in conjunction with metal multi-tooth screws

Features

Suitable for	Enclosure type: VX TS AX wall-mounted housing, 3-part Suitable for width/depth: 1,200 mm Enclosure type: VX TS AX wall-mounted housing, 3-part Suitable for width/depth: 47.2 "
Suitable for	AX base/plinth system VX base system
Packaging unit	6 pc(s).
Net weight	4.68
Gross weight	4.86
PCF per pack (cradle-to-gate)	19 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177114654
ETIM 9	EC000386
ETIM 8	EC000386
ECLASS 8.0	27400602