Rittal – The System.

Faster – better – everywhere.



AS 4054.030

Flex crimping tool

State: 11/14/2026 (Source: www.rittal.com/us-en)

AS 4054.030 - Flex crimping tool For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.





Features

Model No.	AS 4054.030
Version	Straight
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Front or side mounting of the wire end ferrule through a rotatable head Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Unlockable forced lock Self-adjusting
Material	High-grade special tool steel
Surface finish	Coated, black, matt
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Trapezoid crimp
Cable entry direction	front and side
Dimensions	Length: 180 mm Length: 7.09 ˝
AWG	26 - 8
For cross section	0.14 - 10 mm²

© Rittal 2026

Features

Packaging unit	1 pc(s).
Net weight	0.35 kg
Gross weight	0.388 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	AS crimping tool for cross-section 0.14 – 10 mm², rotating head, trapezoidal crimp