

Rittal – The System.

Faster – better – everywhere.



AS 4054.080 Crimping tool

State: 4/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.080 - Crimping tool For crimp tab terminals

For machining non-insulated tab receptacles



Features

Model No.	AS 4054.080
Version	Angled
Product description	For crimping non-insulated crimp tab terminals.
Benefits	Unlockable forced lock Labeled die stations for precise machining of the relevant cross sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	B-crimp
Dimensions	Width: 18 mm Height: 59 mm Length: 198 mm Width: 0.71 " Height: 2.32 " Length: 7.8 "
AWG	26 - 16
For cross section	0.1 - 1.5 mm ²
Packaging unit	1 pc(s).
Net weight	0.433 kg

Features

Gross weight	0.443 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping pliers for crimp tab terminals
