

Rittal – The System.

Faster – better – everywhere.



AS 4055.116

Round split plate punching machine

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.116 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.116 |
| Version | With 3-way split |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | Die Stamp |
| Workable material | Stainless steel |
| Max. material thickness that can be machined for stainless steel | 2 mm |
| Ø hole punch | 16.2 mm |
| For thread | M16 |
| Note | Tension screws with a ball bearing must be used when operating with a wrench |
| Suitable for hydraulic bolt order number | 4055.665 |
| Tension screw (Ø x L) | 11.1 x 60 mm |
| Hydraulic tension screw Ø | 11.1 mm 19 cm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.043 kg |
| Gross weight | 0.059 kg |
| Customs tariff number | 82073010 |
| ETIM 9 | EC000156 |

Features

| | |
|---------------------|--|
| ETIM 8 | EC000156 |
| ECLASS 8.0 | 21049047 |
| Product description | Splitter hole punch, round for stainless steel, round, with triple splitting |
