


# Rittal – The System.

Faster – better – everywhere.



## VX 5302.120 Cable route

State: 6/1/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.120 - Cable route for VX, VX IT

For cable clamping and routing for network and server applications.



## Features

Model No.	VX 5302.120
Benefits	Easy mounting with tool-free quick-release fastening Alternatively suitable for screw-fastening Integrated multi-function perforation for fixing cable routing elements Integrated mounting holes for fixing the PDUs in a 7 U pitch pattern via a keyhole holder
Applications	For vertical cable routing and strain relief for network and server applications
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Assembly components
Installation options	On the VX IT frame between the roof and base frame, all round Alternatively, a screw fastening between the upper and lower depth stays is possible in 800 mm wide VX IT racks

# Features

Mounting tip	Assembly is by means of quick attachment across the entire cabinet depth on the enclosure frame. For installation in 800 mm wide cabinets, an additional screw connection to the depth stays of the 19" installation is possible
Dimensions	Width: 145 mm Width: 5.71 "
Suitable for	Enclosure type: VX VX IT Height: = 2,000 mm Enclosure type: VX VX IT Height: = 78.7 "
Packaging unit	1 pc(s).
Net weight	4.4 kg
Gross weight	4.56 kg
PCF/VE (cradle-to-gate)	18.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83024200
ETIM 9	EC000047
ECLASS 8.0	27400703
Product description	Cable route, for VX, VX IT, for vertical cable routing and strain relief, for network and server applications, integrated multifunction punchings for fastening