


Rittal – The System.

Faster – better – everywhere.



AS 4055.116

Round split plate punching machine

State: 9/3/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.116 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.116
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp
Workable material	Stainless steel
Max. material thickness that can be machined for stainless steel	2 mm
Ø hole punch	16.2 mm
For thread	M16
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.665
Tension screw (Ø x L)	11.1 x 60 mm
Hydraulic tension screw Ø	11.1 mm 19 cm
Packaging unit	1 pc(s).
Net weight	0.043
Gross weight	0.059
Customs tariff number	82073010
EAN	4028177807983

Features

ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047