Rittal – The System.

Faster – better – everywhere.





DK 5302.200 Blanking panel, 19" (482.6 mm)

State: 11/26/2025 (Source: rittal.com/us-en)



DK 5302.200 - Blanking panel, 19" (482.6 mm) Tool-free attachment

Enables fast, tool-free fastening and thermal partitioning of unconfigured mounting surfaces in a 482.6 mm (19"), 1 U pitch pattern.

Features

Model No.	DK 5302.200
Benefits	Larger areas may be covered by combining multiple units.
	Versatile panel for individual requirements. Extendible on both sides with additional panels.
	Repeated removal and re-use possible
Material	Plastic
	Fire behavior according to UL 94 HB, halogen-free
Surface finish	Matt
Color	RAL 9005
Supply includes	Blanking panel, 1 U, with integral quick-fastening
Build-up height	1 U
Dimensions	Width: 482.6 mm
	Width: 19 "
Height units	1 U
Packaging unit	5 pc(s).
PCF/VE (cradle-to-gate)	1.99 KG CO2e
Customs tariff number	73269098
EAN	4028177955646
ETIM 9	EC000456
ECLASS 8.0	27189217

© Rittal 2025