

Rittal – The System.

Faster – better – everywhere.



AS 4055.120

Round split plate punching machine

State: 2/13/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.120 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.120 |
| Version | With 3-way split |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | Die Stamp |
| Workable material | Stainless steel |
| Max. material thickness that can be machined for stainless steel | 2 mm |
| Ø hole punch | 20.4 mm |
| For thread | M20 |
| Note | Tension screws with a ball bearing must be used when operating with a wrench |
| Suitable for hydraulic bolt order number | 4055.665 |
| Tension screw (Ø x L) | 11.1 x 60 mm |
| Hydraulic tension screw Ø | 11.1 mm 19 cm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.077 |
| Gross weight | 0.098 |
| Customs tariff number | 82073010 |
| EAN | 4028177808003 |

Features

ETIM 9 EC000156

ETIM 8 EC000156

ECLASS 8.0 21049047