


# Rittal – The System.

Faster – better – everywhere.



## DK 5501.410 Slide rail, 1U, fixed installation

State: 6/16/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.410 - Slide rail, 1U, fixed installation for VX IT, TS IT, TX CableNet

Mounted between front and rear mounting levels.

## Features

Model No.	DK 5501.410
Product description	Side system punchings to mount accessories and ventilate active components that exhaust air from the side.
Benefits	Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels
Applications	For assembly on the front mounting level To support heavy installed equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between mounting levels	345 mm 13.6 "
Length	275 mm 10.8 "
Installation options	for 19" standard profile rails
Mounting tip	The 19" space between levels in the VX IT must be adjusted accordingly prior to installation
Load capacity	800 N, static
Note	Effective contact surface 35 mm per side
Contact surface	Width: 35 mm Width: 1.38 "
Suitable for	Enclosure type: VX IT TS IT TX CableNet

# Features

Packaging unit	2 pc(s).
Net weight	0.74 kg
Gross weight	0.82 kg
PCF/VE (cradle-to-gate)	3.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Slide rail, 1 U, D: 275 mm, 80 kg, static, For two 482.6 mm (19") attachment level (front+rear), distance between levels:: 345 mm, static installation, for 482.6 mm (19") system punchings