

**Rittal – The System.**

Faster – better – everywhere.



# DK 5501.460

## Slide Rails, 1U, Depth-Variable

State: 4/22/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.460 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .



## Features

Model No.	DK 5501.460
Benefits	Tool-free, time-saving one-person assembly from the front of the enclosure All three mounting holes in the EIA system punchings are available for screw-fastening the equipment Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible
Applications	For assembly on the front mounting level To support heavy installed equipment. To adapt to individual distances between 19" levels
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear for 19" standard profile rails
Load capacity	800 N
Note	Effective contact surface 25 mm per side

# Features

Suitable for	Enclosure type: VX IT TE TX CableNet
Distance between levels	400 - 600 mm 15.7 - 23.6 "
Packaging unit	2 pc(s).
Net weight	2.164 kg
Gross weight	2.34 kg
PCF/VE (cradle-to-gate)	9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Slide rail, support surface width: 25 mm, depth-variable, 80 kg, For two 482.6 mm (19")-mounting angles (front+rear), distance between levels:: 400-600 mm