

Rittal – The System.

Faster – better – everywhere.



AS 4055.180

Metric split plate punching machine set

State: 7/5/2025 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.180 - Metric split plate punching machine set For stainless steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.180
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 dies 5 stamps Plastic case
Workable material	Stainless steel
Max. material thickness that can be machined for stainless steel	2 mm 2 mm 2 mm 2.5 mm 2.5 mm
Ø hole punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For thread	M16 M20 M25 M32 M40
Note	Tension screws with a ball bearing must be used when operating with a wrench

Features

Suitable for hydraulic bolt order number	4055.665
	4055.665
	4055.665
	4055.663
	4055.663

Packaging unit	1 pc(s).
----------------	----------

Net weight	0.849
------------	-------

Gross weight	1.098
--------------	-------

Customs tariff number	82034000
-----------------------	----------

EAN	4028177808171
-----	---------------

ETIM 9	EC002121
--------	----------

ETIM 8	EC002121
--------	----------

ECLASS 8.0	21049047
------------	----------
