

Rittal – The System.

Faster – better – everywhere.



DK 5501.625

Component Shelf 2 U, Static Installation

State: 6/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.625 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.



Features

| | |
|-------------------------|--|
| Model No. | DK 5501.625 |
| Version | 19" |
| Product description | Mounted on vertical 482.6 mm (19") rails. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 9005 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm Depth: 400 mm Width: 19 " Depth: 15.7 " |
| Packaging unit | 1 pc(s). |
| Net weight | 3.297 kg |
| Gross weight | 3.52 kg |
| PCF/VE (cradle-to-gate) | 11.4 kg CO2 eq (Cat B) |

Features

| | |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WHD: 482,6x2 Ux400 mm, 25 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 9005 |