

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.180**

**Metric split plate punching machine set**

State: 2/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4055.180 - Metric split plate punching machine set For stainless steel, with 3-way pitch

For punching round cut-outs

## Features

Model No.	AS 4055.180
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 dies 5 stamps Plastic case
Workable material	Stainless steel
Max. material thickness that can be machined for stainless steel	2 mm 2 mm 2 mm 2.5 mm 2.5 mm
Ø hole punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For thread	M16 M20 M25 M32 M40
Note	Tension screws with a ball bearing must be used when operating with a wrench

# Features

---

Suitable for hydraulic bolt order number	4055.665 4055.665 4055.665 4055.663 4055.663
Packaging unit	1 pc(s).
Net weight	0.849
Gross weight	1.098
Customs tariff number	82073010
EAN	4028177808171
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049047

---