


**Rittal – The System.**

Faster – better – everywhere.



**DK 5501.625**

**Component Shelf 2 U, Static  
Installation**

State: 2/1/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL



IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 5501.625 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.



## Features

|                         |  |
|-------------------------|--|
| Model No.               | DK 5501.625  |
| Version                 | 19"  |
| Product description     | Mounted on vertical 482.6 mm (19") rails.                        |
| Material                | Carbon steel   |
| Surface finish          | Spray-finished   |
| Color                   | RAL 9005   |
| Load capacity           | 25 kg surface load, static                                       |
| Note                    | Not suitable for combination with telescopic slides.             |
| Dimensions              | Width: 482.6 mm<br>Depth: 400 mm<br>Width: 19 "<br>Depth: 15.7 " |
| Packaging unit          | 1 pc(s).   |
| Net weight              | 3.297  |
| Gross weight            | 3.52   |
| PCF/VE (cradle-to-gate) | 11.4 kg CO2 eq (Cat B)   |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 73269098   |
| EAN                                 | 4028177679061  |
| E-Number Sweden                     | E7239586   |
| ETIM 9                              | EC002620   |
| ECLASS 8.0                          | 27189261   |

---