
Rittal – The System.

Faster – better – everywhere.





State: 11/18/2025 (Source: rittal.com/us-en)

SAMAN

BANANA

MANAAN!

CAMANA

CARARA

AND W

money

CANADA

MANAN

WALL WALL

mond

TAN VIV

MANN

VAV VAN

DK 5502.100 - Cable duct for TS IT

Cable duct hinged on both sides, removable cable cover.



Features

Model No.	DK 5502.100
Product description	Cable duct for concealed cable routing. Easy access to the cabling via the hinged duct covers at any time, optionally removable. The duct has cable entry options to the inside of the enclosure and through the duct's rear wall. The cable retaining bars supplied with the duct can be snapped onto the cable fingers in the duct with variable depth to support the cable routing. Alternatively, the cable duct can be screw-fitted. Can be combined with the brush kit TS IT for optimized air routing.
Benefits	Easy mounting with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying Cable duct can be used as a partitioning component against air short circuits within a cold aisle containment Lockable cable ducts can be fitted with 1 U mounting standard expansion components
Material	Carbon steel Plastic to UL 94-HB
Color	RAL 9005
Supply includes	Cover and assembly components 4 cable retainers for spare cables

© Rittal 2025

Features

Installation options	In TS IT with 19" profile rails, height 2000 mm
	In TS IT with 482.6 mm (19") mounting frame, height 1800 mm
	In TE 8000 with 482.6 mm (19") mounting frame, height 2000 mm
	In the Data Rack with 40 U
Height units	38 U
Dimensions	Width: 95 mm
	Height: 1,689 mm
	Depth: 150 mm
	Width: 3.74 ″
	Height: 66.5 "
	Depth: 5.91 "
Packaging unit	1 pc(s).
Net weight	7.8
Gross weight	8.16
Customs tariff number	73269098
EAN	4028177811874
ETIM 9	EC000012
ECLASS 8.0	27400703

© Rittal 2025 3