

Rittal – The System.

Faster – better – everywhere.



DK 5502.101 Cable duct

State: 12/10/2025 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.101 - Cable duct for TS IT

Cable duct hinged on both sides, removable cable cover.



Features

Model No.	DK 5502.101
Product description	Cable duct for concealed cable routing. Easy access to the cabling via the hinged duct covers at any time, optionally removable. The duct has cable entry options to the inside of the enclosure and through the duct's rear wall. The cable retaining bars supplied with the duct can be snapped onto the cable fingers in the duct with variable depth to support the cable routing. Alternatively, the cable duct can be screw-fitted. Can be combined with the brush kit TS IT for optimized air routing.
Benefits	Easy mounting with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying Cable duct can be used as a partitioning component against air short circuits within a cold aisle containment Lockable cable ducts can be fitted with 1 U mounting standard expansion components
Material	Carbon steel Plastic to UL 94-HB
Color	RAL 9005

Features

Supply includes	Cover and assembly components 4 cable retainers for spare cables
Installation options	In TS IT with 19" profile rails, height 2200 mm In TS IT with 482.6 mm (19") mounting frame, height 2000 mm In the Data Rack with 45 U
Height units	42 U
Dimensions	Width: 95 mm Height: 1,866 mm Depth: 150 mm Width: 3.74 " Height: 73.5 " Depth: 5.91 "
Packaging unit	1 pc(s).
Net weight	8.46
Gross weight	8.86
Customs tariff number	73269098
EAN	4028177814448
ETIM 9	EC000012
ECLASS 8.0	27400703