### Rittal – The System.

Faster – better – everywhere.







# AS 4055.240 Hole punch, round

State: 11/9/2025 (Source: rittal.com/us-en)



## AS 4055.240 - Hole punch, round for carbon steel

For punching round cut-outs

#### **Features**

Model No.	AS 4055.240
Version	With 3 cutting tips
Supply includes	Die Stamp Tension screw without ball bearing
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	3 mm
Ø hole punch	40.5 mm
For thread	M40
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Net weight	0.522
Gross weight	0.554
Customs tariff number	82073010
EAN	4028177808300
ETIM 9	EC000156
ETIM 8	EC000156

© Rittal 2025

#### Features

ECLASS 8.0

21049047

© Rittal 2025 3