

Rittal – The System.

Faster – better – everywhere.



AS 4055.474

Hole punch, sub-D

State: 12/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.474 - Hole punch, sub-D for carbon steel and stainless steel

For punching rectangular cut-outs for connectors

Features

Model No.	AS 4055.474
Product description	For punching rectangular cut-outs for connectors. The hole punch is operated with a wrench or hydraulic punch.
Benefits	With side chute for waste No jamming of die Anti-rotation axles for stamps and dies are used as tension bolts.
Supply includes	Die Stamp Tension bolts Lock nut Thrust nut with ball bearing Adapter for hydraulics Plastic case
Workable material	Carbon steel Stainless steel
Max. material thickness that can be machined for stainless steel	1 mm
Max. material thickness that can be machined for sheet steel	1.65 mm
Ø hole punch	55.7 x 13.9 mm
Packaging unit	1 pc(s).
Net weight	0.89
Gross weight	0.903
Customs tariff number	82073010
EAN	4028177808591

Features

ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047