### Rittal – The System.

Faster – better – everywhere.





## DK 5526.141 TS IT Network/Server Enclosure

State: 12/8/2025 (Source: rittal.com/us-en)



# DK 5526.141 - TS IT Network/Server Enclosure with glazed door, with 19" mounting frame

TS IT, closed for direct enclosure-related air conditioning. 19" interior installation with 19" mounting frame for a load capacity of up to 1,500 kg, available in a range of size variants.

#### **Features**

Model No.	DK 5526.141
Material	Carbon steel
	Aluminum
	Viewing door: Single-pane safety glass, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Interior installation: Dipcoat-primed
	Doors and roof: Dipcoat-primed, powder coated
General color	RAL 7035
Color	Housing frame and panels: RAL 7035
	Interior installation: RAL 9005
Supply includes	Enclosure frame TS 8 with doors and roof plate
	Glazed aluminum door, front, 180° hinges
	Lock front and rear: Comfort handle for semi-cylinders and security
	lock 3524 E
	Two 482.6 mm (19") mounting frames, front and rear, depth-variable
	Spacers, height 50 mm, for raising the cover plate above the fan
	breakout in the roof panel, for passive ventilation (enclosed) Not
	required for variants without cutout.
	Connection accessories for potential equalization with earthing
	point (supplied loose)
	12 x 19" fasteners 1 U, contacting (supplied)
	50 multi-tooth screws, conductive (supplied loose)
	IPPC pallet
	Roof plate, multi-piece, removable, for horizontal cable entry at the
	rear and covered cut-out for fan mounting plate
	Carbon steel door at the rear, 180° hinges

© Rittal 2025 2

#### Features

Dimensions	Width: 600 mm
	Height: 1,200 mm
	Depth: 600 mm
	Width: 23.6 "
	Height: 47.2 "
	Depth: 23.6 "
Height units	24 U
Height units	24 U
Mounting space to 19" level, front/	84 mm / 168 mm
rear	
Distance between levels as	345 mm
delivered	13.6 <i>"</i>
Design doors	Solid
Design of 19" mounting level(s)	Mounting frame, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	67.1
Gross weight	70.6
EAN	4028177705838
E-Number Sweden	E7239870
ETIM 9	EC002499
ECLASS 8.0	27180207

## Approvals

© Rittal 2025 3

## Approvals

Certificates	Surface finish
Explanations	Declaration of conformity

© Rittal 2025