

Rittal – The System.

Faster – better – everywhere.



AS 4055.547

Round split plate punching machine

State: 1/9/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.547 - Round split plate punching machine For sheet steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.547
Version	With 3-way split
Product description	
Supply includes	Die Stamp
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	3 mm
Ø hole punch	47 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Net weight	0.467
Gross weight	0.509
Customs tariff number	82073010
EAN	4028177808768
ETIM 9	EC000156

Features

ETIM 8 EC000156

ECLASS 8.0 21049047