

Rittal – The System.

Faster – better – everywhere.



AS 4055.581

Split plate punching machine set M12 to M40

State: 8/16/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.581 - Split plate punching machine set M12 to M40 For sheet steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.581
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	6 dies 6 stamps Tension screw with ball bearing, Ø 6 x 40 mm Tension screw with ball bearing, Ø 9.5 x 50 mm Tension screw with ball bearing, Ø 19 x 55 mm HSS pilot drill Ø 10 mm 1 can of lubricating paste Plastic case
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	1.5 mm 2 mm 2 mm 2 mm 3 mm 3 mm
Ø hole punch	12.5 mm 16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm

Features

For thread	M12 M16 M20 M25 M32 M40
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.660 4055.661 4055.661 4055.661 4055.663 4055.663
Packaging unit	1 pc(s).
Net weight	2.2
Gross weight	2.256
Customs tariff number	82073010
EAN	4028177808843
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21044719