

Rittal – The System.

Faster – better – everywhere.



AS 4055.700

Busbar bending and hole punching unit CW 120-S

State: 8/6/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.700 - Busbar bending and hole punching unit CW 120-S

The bending and hole punching unit from the CW 120-S product range is suitable for bending and punching busbars. Round holes and slots can be punched. The integrated precision laser makes the cutting and bending process easier. The bending and hole-punching unit can simply be placed on a workbench.



Features

Model No.	AS 4055.700
Version	Electrical protractor Length stop Mandrel R10 Bending die
Product description	The bending and hole punching unit from the CW 120-S product range is suitable for bending and punching busbars. Round holes and slots can be punched. The bending and hole-punching unit can simply be placed on a workbench.
Benefits	High level of bending and punching accuracy Simple tool change
Material thickness:	12 mm 0.47 "
Stamping/material width (max.)	120 mm
Bending/Leg length (min.)	50 mm
U-Bend (min.)	100 mm
Z-Bend (min.)	72 mm
Bending angle (max.)	90 °

Features

Note	Leg length at a Z-bend depends on the material thickness
Bending (max.)	120 x 12 mm
Stamping (max.)	6.6 x 21.5 mm
Machine dimensions	Width: 700 mm Height: 410 mm Depth: 461 mm
Support area	Width: 756 mm Height: 426 mm Depth: 461 mm Width: 29.8 " Depth: 18.1 "
Packaging unit	1 pc(s).
Net weight	64.5
Gross weight	67.5
Customs tariff number	84624900
EAN	4028177920668
ETIM 9	EC004303
ETIM 8	EC004303
ECLASS 8.0	36600804

Approvals

Explanations	Declaration of conformity
--------------	---------------------------