

Rittal – The System.

Faster – better – everywhere.



AS 4055.720 Electro-hydraulic pump

State: 8/21/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.720 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive the products from the CW 120-S product range.

Features

| | |
|--|---|
| Model No. | AS 4055.720 |
| Product description | The electro-hydraulic pump is used to drive the products from the CW 120-S product range. |
| Rated power | 1.3 kW |
| Filling volume | 3.2 l |
| Working volume | 2.2 l |
| Flow rate (max.) | 1.1 l/min |
| Oil (type) | HLP 46 |
| Rated operating voltage | 230 V, 50 Hz |
| Rated current | 5.65 A |
| Machine dimensions | Width: 400 mm Height: 325 mm Depth: 335 mm |
| Support area | Width: 402 mm Height: 342 mm Depth: 397 mm Width: 15.8 " Depth: 15.6 " |
| Permissible operating pressure (p. max.) | 700 bar 10,152.6 PSI |
| Packaging unit | 1 pc(s). |
| Net weight | 32 |
| Gross weight | 34.5 |
| Customs tariff number | 84138100 |
| EAN | 4028177920644 |

Features

| | |
|------------|----------|
| ETIM 9 | EC011047 |
| ETIM 8 | EC011047 |
| ECLASS 8.0 | 27301290 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|