

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.730 Electro-hydraulic pump

State: 4/28/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.730 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive the products from the CW 120-S product range.

## Features

Model No.	AS 4055.730
Product description	The electro-hydraulic pump is used to drive the products from the CW 120-S product range.
Rated power	1.1 kW
Filling volume	3.5 l
Working volume	2.2 l
Flow rate (max.)	1.1 l/min
Oil (type)	HLP 46
Rated operating voltage	230 V, 50 Hz
Rated current	6.5 A
Machine dimensions	Width: 405 mm Height: 405 mm Depth: 310 mm
Support area	Width: 505 mm Height: 505 mm Depth: 497 mm Width: 19.9 " Depth: 19.6 "
Permissible operating pressure (p. max.)	630 bar 9,137.4 PSI
Packaging unit	1 pc(s).
Net weight	32 kg
Gross weight	34.5 kg
Customs tariff number	84135061
ECLASS 8.0	27301290

# Approvals

---

Explanations

Declaration of conformity