Rittal – The System.

Faster – better – everywhere.



CP 6148.000

Twin castors

State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CP 6148.000 - Twin castors

For mobile use, can be mounted directly on the enclosure.

Features

Model No.	CP 6148.000
Product description	For mobile use, can be mounted directly on the enclosure.
Color	Black with gray running surface
Supply includes	4 twin castors, 2 x with, 2 x without locks. Assembly components
Suitable for	Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: CX Enclosure type: PC Enclosure type: One-piece console, stainless steel Enclosure type: IW Enclosure type: Data Rack Enclosure type: Blue e+ chiller Enclosure type: VX25 TopTherm chiller
Clearande floor	85 mm 3.35 ″
Max. load capacity (static) per component	750 N 168.607 lbf.
Suitable for Model No.	6106.200 6106.300
Dimensions	Thread: M12 x 20
Packaging unit	4 pc(s).
Customs tariff number	39269097
ETIM 9	EC002621
ECLASS 8.0	27189262

Features

Product description	CP Twin castors, 2 each with/without lock, static load per castor 75 kg