

Rittal – The System.

Faster – better – everywhere.



CP 6340.300 Compact Panel

State: 5/16/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6340.300 - Compact Panel

Command panel in an elegant design made from extruded aluminium sections. Ideal for small operator panels. Versatile interior installation

Features

Model No.	CP 6340.300
Version	With support arm connection 90 x 71 mm for CP 40, steel
Product description	For small operating units built into front panels. The front panel is inserted from the rear and secured with screw clamps. Special front panels with a material thickness of between 2 and 6 mm are possible. Rear panel optionally hinged on the left or right. Roof tray with cut-out and reinforcement for CP 40 support arm system, steel.
Material	Roof tray, base tray: die-cast zinc Rear wall: Aluminum Side parts: Extruded aluminum section Screw cover: Plastic
Surface finish	Roof tray, base tray, side parts: Powder-coated Rear panel: Natural anodized
Color	RAL 7024
Supply includes	Roof tray Base tray Rear panel Side parts Screw cover Seal and screw clamp
Dimensions	Width: 315 mm Height: 238 mm Depth: 87 mm Width: 12.4 " Height: 9.37 " Depth: 3.43 "
Protection category IP to IEC 60529	IP 65

Features

Protection category NEMA	NEMA 12
Suitable for front panel width	252 mm 9.92 "
Suitable for front panel height	200 mm 7.87 "
Base material	Aluminum
Packaging unit	1 pc(s).
Weight/packaging unit	3.4 kg 7.5 lb.
Customs tariff number	94032080
EAN	4028177382718
ETIM 7.0	EC002504
ECLASS 8.0	27180505

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---