Rittal – The System.

Faster – better – everywhere.



# CP 6372.562
# Comfort Panel

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# CP 6372.562 - Comfort Panel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability. Protection category IP 65 to IEC 60 529.





## Features

| | |
|---|---|
| Model No. | CP 6372.562 |
| Version | Support arm connection Ø 130 mm |
| Benefits | Aluminum housing, high thermal conductivity for optimum passive heat dissipation.<br>Low weight coupled with high stability<br>Compatible with all Rittal stand and support arm systems |
| Material | Housing: Extruded aluminum section<br>Corner pieces: Die-cast zinc<br>Corner protectors: Plastic |
| General color | Natural anodized |
| Color | Housing: Natural anodized.<br>Corner pieces: RAL 7035<br>Corner protectors: Similar to RAL 7024 |
| Supply includes | Enclosure with cut-out for support arm connection<br>3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C<br>Seals and assembly components for front panels<br>Hinged rear panel, hinging on the longest side |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 628.5 mm<br>Height: 708.5 mm<br>Depth: 170 mm<br>Width: 24.7 ″<br>Height: 27.9 ″<br>Depth: 6.69 ″ |
| Installation depth | 152 mm<br>5.98 ″ |
| Protection category IP to IEC 60 529 | IP 65 |
| Protection category NEMA | NEMA 12 |
| Suitable for front panel width | 520 mm<br>20.5 ″ |
| Suitable for front panel height | 600 mm<br>23.6 ″ |
| Version | Service access from rear |
| Note | The support arm connection may be swapped over by rotating the enclosure |
| Base material | Aluminum |
| Lock | Lock version: Cam<br>No. of locks: 3<br>Lock Insert: 3 mm double-bit |
| Packaging unit | 1 pc(s). |
| Net weight | 13.5 kg |
| Gross weight | 20.32 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002504 |
| ECLASS 8.0 | 27180505 |
| Product description | CP Compact Panel, for front panel BH 520x600 mm, installation depth 152 mm, Extruded aluminum section, Support arm connection Ø 130 mm, Hinged rear panel with cam |

# Approvals

| Approvals | UL + C-UL (listed) |
| --- | --- |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |