

Rittal – The System.

Faster – better – everywhere.



VX 5302.025 Combination rails

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.025 - Combination rails for VX, VX IT, TX CableNet

Combination of C rail for cable clamping with cable clamps and a cable guide rail with hammer heads for cable routing. The cables can optionally be secured to the combination rail with cable clamps, cable ties, or Velcro fasteners to be relieved of strain.

Features

| | |
|----------------------|--|
| Model No. | VX 5302.025 |
| Product description | Combination of C rail for cable clamping with cable clamps and a cable guide rail with hammer heads for cable routing. The cables can optionally be secured to the combination rail with cable clamps, cable ties, or Velcro fasteners to be relieved of strain. |
| Benefits | May be installed on either the outside or inside of the enclosure frame |
| Applications | For cable routing and strain relief of the routed cables on the VX enclosure frame |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options | Direct screw-fastening between the vertical uprights of the enclosure frame |
| Suitable for | Enclosure type: VX VX IT Width: = 1,200 mm Depth: = 1,200 mm Enclosure type: VX VX IT Width: = 47.2 " Depth: = 47.2 " |
| Suitable for width | 1,200 mm 47.2 " |
| Packaging unit | 4 pc(s). |

Features

| | |
|-------------------------------------|--|
| Net weight | 2.8 kg |
| Gross weight | 3.16 kg |
| PCF/VE (cradle-to-gate) | 11.5 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | Combination rail for VX IT, for cable routing and strain relief of routed cables on the VX frame structure, for enclosure width 1,200 mm, for enclosure depth 1,200 mm |