

# Rittal – The System.

Faster – better – everywhere.



## CX 6720.000

## CX Console Top-Section

State: 5/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CX 6720.000 - CX Console Top-Section

Four widths offer the best conditions for individual monitoring and a three-part construction of the CX desk system.



## Features

Model No.	CX 6720.000
Version	Top piece
Product description	Four widths offer the best conditions for individual monitoring and a three-part construction of the CX desk system.
Material	Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing Cover hinged at bottom, including cover retainer Open base for individual cable entry Lock: 3 mm double-bit
Dimensions	Width: 600 mm Height: 515 mm Width: 23.6 " Height: 20.3 "
Top depth	125 mm 4.92 "
Bottom depth	245 mm 9.65 "

# Features

IK code	IK10
Note	For a 3-piece console setup, a desk unit and pedestal are required
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Base material	Carbon steel
Dimensions	Width: 600 mm Height: 515 mm Top depth: 125 mm Bottom depth: 245 mm Width: 23.6 " Height: 20.3 " Top depth: 4.92 " Bottom depth: 9.65 "
No. of locks	2
Lock version	Cam
Lock Insert	3 mm double-bit
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	15 kg
Gross weight	16.8 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	CX console system, console top-section for 3-piece setup, width: 600 mm, carbon steel

# Approvals

---

Approvals

UL + C-UL (listed)

---

Explanations

Declaration of conformity