Rittal – The System.

Faster – better – everywhere.



TP 6740.600

TP Consoles

State: 11/10/2026 (Source: www.rittal.com/us-en)

TP 6740.600 - TP Consoles

One-piece console for operating and monitoring, with large mounting plate and a high protection category of IP 55, available in four different widths. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

Model No.	TP 6740.600
Material	Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing, solid back and sides Door or double door at front, with locking rod Mounting panel Cover hinged at rear, 2 stays with automatic locking. Unlatching automatically on the left, manually on the right Base Plates
Dimensions	Width: 1,000 mm Height: 975 mm Depth: 400 mm Width: 39.4 ″ Height: 38.4 ″ Depth: 15.7 ″
Dimensions of mounting plate (W x H)	930 mm x 900 mm 36.6 ″ x 35.4 ″
Top depth	500 mm 19.7 ″
Bottom depth	400 mm 15.7 ″

© Rittal 2026

Features

Number of doors	2
IK code	IK08
Note	The sliding element VX 5051.172 can be used as a mounting aid for the VX base/plinth system, new design
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Base material	Carbon steel
Dimensions	Width: 1,000 mm Height: 975 mm Top depth: 500 mm Bottom depth: 400 mm Width: 39.4 ″ Height: 38.4 ″ Top depth: 19.7 ″ Bottom depth: 15.7 ″
Packaging unit	1 pc(s).
Net weight	73 kg
Gross weight	75 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	TP upright console, WxHxD1/D2: 1000x975x400/500 mm, carbon steel

Approvals

Approvals	UL + C-UL (listed)

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK