

Rittal – The System.

Faster – better – everywhere.



DK 5302.052 Cable duct

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.052 - Cable duct for VX IT, TX CableNet, Data Rack

Cable duct hinged on both sides, removable cable cover.

Features

| | |
|--------------------------|---|
| Model No. | DK 5302.052 |
| Product description | Cable duct for concealed cable routing. Easy access to the cabling via the hinged duct covers at any time, optionally removable. The duct has cable entry options to the inside of the enclosure and through the duct's rear wall. The cable retaining bars supplied with the duct can be snapped onto the cable fingers in the duct with variable depth to support the cable routing. Alternatively, the cable duct can be screw-fitted. Can be combined with the brush kit VX IT for optimized air routing. |
| Benefits | Easy mounting with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying Cable duct can be used as a partitioning component against air short circuits within a cold aisle containment Lockable cable ducts can be fitted with 1 U mounting standard expansion components |
| Technical specifications | Integrated 19" mounting cut-outs (1 U): 6 pc(s). |
| Material | Carbon steel Plastic to UL 94-HB |
| Color | RAL 9005 |
| Supply includes | Cable duct 2 covers 14 cable fingers, 6 U 10 cable retention bars Assembly components |
| Height units | 42 U |
| Suitable for | Cannot be combined with 19" profile rails, dynamic, for VX IT |

Features

| | |
|-------------------------------------|--|
| Note | This cannot be combined with 19" profile rails dynamic for symmetrical interior installation in enclosure type VX IT, for asymmetrical interior installation one-sided mounting is possible. |
| Dimensions | Width: 109.5 mm Depth: 314.5 mm Length: 1,872 mm Width: 4.31 " Depth: 12.4 " Length: 73.7 " |
| Suitable for | Enclosure type: VX IT Data Rack TX CableNet Width: = 800 mm Height: = 2,000 mm = 2,122 mm Enclosure type: VX IT Data Rack TX CableNet Width: = 31.5 " Height: = 78.7 " = 83.5 " |
| Suitable for width | 800 mm 31.5 " |
| Packaging unit | 1 pc(s). |
| Net weight | 9.2 kg |
| Gross weight | 9.54 kg |
| PCF/VE (cradle-to-gate) | 32.6 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000012 |
| ECLASS 8.0 | 27400703 |
| Product description | Cable duct, 42 U, for concealed cable routing. For enclosure width 800 mm, for enclosure height VX IT 2000 mm |