

Rittal – The System.

Faster – better – everywhere.



DK 5302.053 Cable duct

State: 11/5/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.053 - Cable duct for VX IT, TX CableNet, Data Rack

Cable duct hinged on both sides, removable cable cover.

Features

Model No.	DK 5302.053
Product description	Cable duct for concealed cable routing. Easy access to the cabling via the hinged duct covers at any time, optionally removable. The duct has cable entry options to the inside of the enclosure and through the duct's rear wall. The cable retaining bars supplied with the duct can be snapped onto the cable fingers in the duct with variable depth to support the cable routing. Alternatively, the cable duct can be screw-fitted. Can be combined with the brush kit VX IT for optimized air routing.
Benefits	Easy mounting with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying Cable duct can be used as a partitioning component against air short circuits within a cold aisle containment Lockable cable ducts can be fitted with 1 U mounting standard expansion components
Material	Carbon steel Plastic to UL 94-HB
Color	RAL 9005
Supply includes	Cable duct 2 covers 14 cable fingers, 6 U 10 cable retention bars Assembly components
Height units	47 U
Suitable for	Cannot be combined with 19" profile rails, dynamic, for VX IT

Features

Note	This cannot be combined with 19" profile rails dynamic for symmetrical interior installation in enclosure type VX IT, for asymmetrical interior installation one-sided mounting is possible.
Dimensions	Width: 109.5 mm Depth: 314.5 mm Length: 2,099 mm Width: 4.31 " Depth: 12.4 " Length: 82.6 "
Suitable for	Enclosure type: VX IT TX CableNet Width: = 800 mm Height: = 2,200 mm = 2,200 mm Enclosure type: VX IT TX CableNet Width: = 31.5 " Height: = 86.6 " = 86.6 "
Suitable for width	800 mm 31.5 "
Packaging unit	1 pc(s).
Net weight	10.2
Gross weight	10.78
PCF/VE (cradle-to-gate)	39.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177958593
ETIM 9	EC000012
ECLASS 8.0	27400703