


Rittal – The System.

Faster – better – everywhere.



VX 5302.122 Cable route

State: 7/24/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.122 - Cable route for VX, VX IT

For cable clamping and routing for network and server applications.



Features

| | |
|----------------------|--|
| Model No. | VX 5302.122 |
| Benefits | Easy mounting with tool-free quick-release fastening Alternatively suitable for screw-fastening Integrated multi-function perforation for fixing cable routing elements Integrated mounting holes for fixing the PDUs in a 7 U pitch pattern via a keyhole holder |
| Applications | For vertical cable routing and strain relief for network and server applications |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 9005 |
| Supply includes | Assembly components |
| Installation options | On the VX IT frame between the roof and base frame, all round Alternatively, a screw fastening between the upper and lower depth stays is possible in 800 mm wide VX IT racks |

Features

| | |
|-------------------------------------|--|
| Mounting tip | Assembly is by means of quick attachment across the entire cabinet depth on the enclosure frame. For installation in 800 mm wide cabinets, an additional screw connection to the depth stays of the 19" installation is possible |
| Dimensions | Width: 145 mm Width: 5.71 " |
| Suitable for | Enclosure type: VX VX IT Height: = 2,200 mm Enclosure type: VX VX IT Height: = 86.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 4.8 |
| Gross weight | 5.02 |
| PCF/VE (cradle-to-gate) | 19.8 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177952720 |
| E-Number Sweden | E7238518 |
| ETIM 9 | EC000047 |
| ECLASS 8.0 | 27400703 |