

Rittal – The System.

Faster – better – everywhere.



VX 5307.134

VX IT network/server enclosure

State: 6/27/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5307.134 - VX IT network/server enclosure with glazed door, IP 55, with 19" profile rails, standard

VX IT network/server enclosure, closed, for direct enclosure-related air conditioning. 19" interior installation with 19" profile rails in the standard version, available in a range of size variants and in protection classes up to IP 55.



Features

Model No.	VX 5307.134
Material	Carbon steel Aluminum Viewing door: Single-pane safety glass, 3 mm Front door: aluminum, 1.25 mm Back door: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Interior: Spray-finished Rear door and roof: dipcoat-primed, powder-coated Front door: Aluminum, anodized/spray-finished
General color	RAL 7035
Color	Enclosure frame, rear door and roof: RAL 7035 Front door: Vertical sections, silver colored and horizontal sections, RAL 9005 Interior installation: RAL 9005 Handle and hinges: RAL 9005

Features

Supply includes	<p>VX cabinet frame with doors and roof plate</p> <p>Glazed aluminum door, front, 180° hinges</p> <p>Carbon steel door rear, closed, one-piece, 130° hinges</p> <p>Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E</p> <p>Profile rails, 482.6 mm (19")</p> <p>Roof plate, one-piece, solid</p> <p>Base tray with base plate, multi-piece, solid</p> <p>Baying seal and sealing kit for base plates (supplied loose)</p> <p>12 x 19" fasteners 1 U, contacting (supplied)</p> <p>25 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 800 mm</p> <p>Width: 31.5 "</p> <p>Height: 78.7 "</p> <p>Depth: 31.5 "</p>
Height units	42 U
Height units	42 U
Mounting space to 19" level, front/rear	150 mm / 130 mm
Instalation position in 19" area	front and rear
Distance between levels as delivered	520 mm 20.5 "
19" attachment	screw-fastened on top and bottom of diagonal crossbeam
Version	Standard
Roof version	One-piece, solid
Design of rear door	Carbon steel door, closed, one-piece, 130° hinges
Design for front door	Glazed aluminum door, solid, one-piece, 180° hinges
Versions of profile rails	19" standard profile rails in VX IT
Floor version	Base tray with base plate, multi-piece, solid
Design of 19" mounting level(s)	front and rear

Features

Design of position of profile rails	19" level, front and rear
Load capacity	8,000 N
Max. load capacity (static) per cabinet according to UL 2416	8,000 N
Protection category IP to EN 60 529	IP 55 only in conjunction with baying seal or screw-fastened side panels
IK code	IK08
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	106.72 kg
Gross weight	119.8 kg
PCF/VE (cradle-to-gate)	295.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Product description	VX IT, 19" mounting angles, standard, front and rear, glazed door, WHD: 800 x 2000 x 800 mm, 42 HE, IP 55

Approvals

Approvals	UL + C-UL (listed)
Certificates	Negative Certificate Surface finish Protection category

Approvals

Explanations

Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK