Rittal – The System.

Faster – better – everywhere.





DK 7030.000 **CMC III Processing Units**

State: 12/1/2025 (Source: rittal.com/us-en)



DK 7030.000 - CMC III Processing Units

The Processing Unit/Compact is the central unit of the CMC III monitoring system. Up to 32/4 external sensors/CAN bus connection units can be connected to the integrated sensors. The units can be connected to the data network via ethernet, configured via web/USB, send alarms via an email server and be connected to a company's network management system via SNMP.



Features

Model No.	DK 7030.000
Product description	Central unit of the CMC III monitoring system. Up to 32/4 external sensors/CAN-Bus connection units can be connected in addition to the integrated sensors.
Benefits	High redundancy due to redundant power supply. Cost savings from optimized space utilization and connection system High flexibility due to modular system. High level of safety due to permanent monitoring of the physical enclosure environment.
Applications	Enclosure monitoring in IT, industry and facility management
Function principle	Central monitoring unit for the CMC III system. Collects measurement data and alerts network management systems or control rooms when freely adjustable limit values are exceeded. Automatic monitoring of inputs and control of remote outputs.
Version	Piezo transducer for acoustic information Time function through real-time clock with NTP
Material	Plastic

Features

Surface finish	Front: Smooth
	Housing: Textured
Color	Housing: RAL 7035
	Front: RAL 9005
Supply includes	Basic system
	Temperature sensor including connection cable (supplied loose)
	Infrared access sensor (integrated)
	Incl. assembly parts for mounting on surfaces
Infrared access sensor	Yes
Integral temperature sensor	Yes
Interface bus system	2 x RJ45 CAN bus
Alarm relay output	Terminal up to 1.5 mm² (max. 24 V DC/1 A)
Interfaces	Mini USB
	1 x USB
	SD storage card slot (max. 32 GB)
	2 digital inputs
Mobile website	For Android and Windows phones
Network interface	Ethernet in line with IEEE 802.3 via 10/100 BaseT Full-Duplex
	10/100 Mbit/s, PoE
Interface UPS	Terminal
	Socket
	PoE (Power over Ethernet)
Serial interface	RJ12
Interface streaming	Axis network camera with VAPIX® version 3
Number of sensors (max.)	32
Note	For increased network security, unencrypted protocols can be
	disabled
LED displays (rear)	Network status
LED displays (front)	Status

Features

Protocols	TCP/IPv4
	TCP/IPv6
	SNMPv1
	SNMPv2c
	SNMPv3
	Telnet
	SSH
	FTP
	SFTP with SSL
	HTTP
	HTTPS with SSL
	NTP
	DHCP
	DNS
	SMTP
	Syslog
	LDAP
	Radius
	OPC-UA
	Modbus/TCP
	RS-232
Dimensions	Width: 138 mm
	Height: 40 mm
	Depth: 132 mm
	Width: 5.43 "
	Height: 1.57 "
	Depth: 5.2 ″
Operating temperature range	0 °C45 °C
	32 °F113 °F
Ambient humidity (non-	595 %
Ambient humidity (non- condensing)	595 %
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.64
Customs tariff number	85311095
EAN	4028177659322

Features

ETIM 9	EC002627	
ETIM 8	EC002627	
ECLASS 8.0	27189253	

Approvals

Approvals	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity