

Rittal – The System.

Faster – better – everywhere.



VX 5309.126

VX IT network/server enclosure

State: 6/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5309.126 - VX IT network/server enclosure with glazed door, with 19" standard profile rails

VX IT network/server enclosure, closed, for direct enclosure-related air conditioning. 19" interior installation with depth-variable 19" profile rails in the standard version, available in a range of size variants.



Features

Model No.	VX 5309.126
Material	Carbon steel Aluminum Viewing door: Single-pane safety glass, 3 mm Front door: aluminum, 1.25 mm Back door: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Interior: Spray-finished Rear door and roof: dipcoat-primed, powder-coated Front door: Aluminum, anodized/spray-finished
General color	RAL 7035
Color	Enclosure frame, rear door and roof: RAL 7035 Front door: Vertical sections, silver colored and horizontal sections, RAL 9005 Interior installation: RAL 9005 Handle and hinges: RAL 9005

Features

Supply includes	<p>VX cabinet frame with doors and roof plate</p> <p>Glazed aluminum door, front, 180° hinges</p> <p>Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E</p> <p>Profile rails, 482.6 mm (19")</p> <p>Spacers, height 50 mm, for raising the cover plate above the fan breakout in the roof panel, for passive ventilation (enclosed) Not required for variants without cutout.</p> <p>12 x 19" fasteners 1 U, contacting (supplied)</p> <p>25 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, with side depth-adjustable cable entry on both sides, prepared for fan mounting plate</p> <p>Carob steel door rear, closed, vertically divided, 180° hinges</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,000 mm</p> <p>Width: 31.5 "</p> <p>Height: 78.7 "</p> <p>Depth: 39.4 "</p>
Height units	42 U
Mounting space to 19" level, front/rear	87 mm / 193 mm
Installation position in 19" area	front and rear
Distance between levels as delivered	720 mm 28.3 "
19" attachment	On depth stays, screw-fastened at the top and bottom
Version	Standard
Roof version	multi-piece, with side depth-adjustable cable entry on both sides, prepared for fan mounting plate
Design of rear door	Carbon steel door rear, closed, vertically divided, 180° hinges
Design for front door	Glazed aluminum door, solid, one-piece, 180° hinges
Versions of profile rails	19" standard profile rails in VX IT
Floor version	open

Features

Design of 19" mounting level(s)	front and rear
Design of position of profile rails	19" level, front and rear
Load capacity	15,000 N
Max. load capacity (static) per cabinet according to UL 2416	12,000 N
IK code	IK08
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	102.2 kg
Gross weight	110.6 kg
PCF/VE (cradle-to-gate)	273.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Product description	VX IT, 19" mounting angles, standard, front and rear, glazed door, WHD: 800 x 2000 x 1000 mm, 42 U

Approvals

Approvals	UL + C-UL (listed)
Certificates	Negative Certificate Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK