

# Rittal – The System.

Faster – better – everywhere.



## PC 5366.150 PC enclosure system

State: 6/16/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PC 5366.150 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs and keyboards. Extremely simple to use and modern design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access.



## Features

|                     |  |
|---------------------|--|
| Model No.           | PC 5366.150  |
| Version             | with glazed door at the top, fold-out keyboard tray and component shelf  |
| Product description | Secure accommodation of all PC components, from monitors, to PCs and keyboards. For ultimate ease of operation in a contemporary design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access. |
| Material            | Housing, door, rear door, mounting compartment, supports: carbon steel<br>Handles, decorative trim panels: Plastic<br>Door trim panels: Aluminum<br>Viewing window: Single-pane safety glass   |
| Surface finish      | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint   |
| General color       | RAL 7035   |
| Color               | Housing, door, decorative trim panels, supports: RAL 7035<br>Handle: RAL 7015<br>Monitor field, door center section: RAL 7015  |

# Features

|                                     |   |
|-------------------------------------|---|
| Supply includes                     | Housing, door, rear door<br>Base Plates<br>Glazed door, top<br>Folding keyboard<br>Component shelf                        |
| Dimensions                          | Width: 600 mm<br>Height: 1,600 mm<br>Depth: 636 mm<br>Width: 23.6 "<br>Height: 63 "<br>Depth: 25 "                        |
| Protection category IP to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 12   |
| Type rating according to UL 50E     | Type 1<br>Type 12   |
| Max. keyboard dimensions (WxHxD)    | 497 x 50 x 250 mm<br>497 x 60 x 200 mm<br>19.6 x 1.97 x 9.84 "<br>19.6 x 2.36 x 7.87 "                                    |
| Base material                       | Carbon steel  |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 85.5 kg   |
| Gross weight                        | 88 kg   |
| PCF/VE (cradle-to-gate)             | 373.4 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared      |
| Customs tariff number               | 94032080  |
| ETIM 9                              | EC002502  |
| ECLASS 8.0                          | 27180501  |
| Product description                 | PC PC enclosure system, WHD: 600x1600x636 mm, Sheet steel, with glazed door at the top, folding keyboard, component shelf |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Certificates | Surface finish  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---