

Rittal – The System.

Faster – better – everywhere.



PC 5386.000 PC enclosure system

State: 4/5/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5386.000 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a contemporary design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access.

Features

Model No.	PC 5386.000
Version	with glazed door at the top, keyboard drawer and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a contemporary design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access.
Material	Housing, door, rear door, mounting compartment, supports: carbon steel Handles, decorative trim panels: Plastic Door trim panels: Aluminum Viewing window: Single-pane safety glass
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated
Color	Housing, door, decorative trim panels, supports: RAL 7035 Handle: Similar to RAL 9006 Monitor field, door center section: RAL 7015
Supply includes	Housing, door, rear door Glazed door, top Keyboard drawer Component shelf
Dimensions	Width: 800 mm Height: 1,600 mm Depth: 636 mm Width: 31.5 " Height: 63 " Depth: 25 "

Features

Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Max. keyboard dimensions (WxHxD)	480 x 70 x 260 mm 18.9 x 2.76 x 10.2 "
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	123.4 kg
Gross weight	126 kg
Customs tariff number	94032080
ECLASS 8.0	27180501
Product description	PC PC enclosure system, WHD: 800x1600x600 mm, Sheet steel, with glazed door at the top, keyboard drawer, component shelf

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK