


# Rittal – The System.

Faster – better – everywhere.



## DK 5501.450 Slide rail, 1U, fixed installation

State: 4/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.450 - Slide rail, 1U, fixed installation for VX IT, TS IT, TX CableNet

Mounted between front and rear mounting levels.

## Features

|                                  |   |
|----------------------------------|---|
| Model No.                        | DK 5501.450   |
| Product description              | Side system punchings to mount accessories and ventilate active components that exhaust air from the side.  |
| Benefits                         | Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels |
| Applications                     | For assembly on the front mounting level<br>To support heavy installed equipment.   |
| Material                         | Carbon steel  |
| Surface finish                   | Zinc-plated   |
| Supply includes                  | Assembly components   |
| Distance between mounting levels | 745 mm<br>29.3 "  |
| Length                           | 675 mm<br>26.6 "  |
| Installation options             | for 19" standard profile rails  |
| Mounting tip                     | The 19" space between levels in the VX IT must be adjusted accordingly prior to installation  |
| Load capacity                    | 800 N, static   |
| Note                             | Effective contact surface 35 mm per side  |
| Contact surface                  | Width: 35 mm<br>Width: 1.38 "   |
| Suitable for                     | Enclosure type: VX IT<br>TS IT  |

# Features

|                                     |   |
|-------------------------------------|---|
| Packaging unit                      | 2 pc(s).  |
| Net weight                          | 1.8 kg  |
| Gross weight                        | 2.02 kg   |
| PCF/VE (cradle-to-gate)             | 7.6 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared  |
| Customs tariff number               | 73269098  |
| ETIM 9                              | EC002620  |
| ECLASS 8.0                          | 27189261  |
| Product description                 | DK Slide rail, 1 U, D: 675 mm, 80 kg, static, For two 482.6 mm (19") attachment level (front+rear), distance between levels: 745 mm, static installation, for 482.6 mm (19") system punchings |