
Rittal – The System.

Faster – better – everywhere.



# DK 5501.615

# Component Shelf 2 U, Static Installation

State: 11/14/2026 (Source: www.rittal.com/us-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES


FRIEDHELM LOH GROUP

# DK 5501.615 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.







## Features

| | |
|---|---|
| Model No. | DK 5501.615 |
| Version | 19" |
| Product description | Mounted on vertical 482.6 mm (19") rails. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 9005 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm<br>Depth: 250 mm<br>Width: 19 ″<br>Depth: 9.84 ″ |
| Height units | 2 U |
| Packaging unit | 1 pc(s). |
| Net weight | 2.078 kg |
| Gross weight | 2.125 kg |
| PCF/VE (cradle-to-gate) | 9.5 kg CO2 eq (Cat B) |

© Rittal 2026

# Features

| | |
|---|---|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WHD: 482,6x2 Ux250 mm, 25 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 9005 |