

# Rittal – The System.

Faster – better – everywhere.



## DK 7240.201 Socket strip

State: 4/28/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7240.201 - Socket strip for IEC 320 Connectors

Socket strips in various designs for attaching into frames, wall-mounted distributors DK (horizontal) or between a pair of 482.6 mm (19") mounting angles.



## Features

---

Model No.

DK 7240.201

---

Product description

The socket strips are available in various country-specific variants with different functional elements. Special attention has been devoted to practical, universal fastening: Variable attachment facilities have been created with an angle bracket which may be inserted in four positions. Hence, for example, the 482 mm-long socket strips may optionally be mounted on 482.6 mm (19") profile rails, the 19" mounting frame, on the enclosure frame, or in the rear section of the wall-mounted distributor. Socket strips with a length greater than 482 mm can only be mounted on the housing frame. The socket strip may be inserted into all sections with a 25 mm hole pattern, without the need for additional mounting accessories. This makes selection much easier, as well as providing additional flexibility and saving on warehousing. Provision has also been made for cable routing of the infeed, and when mounting in the 482.6 mm (19") section there is adequate space to route the infeed between the socket strip and the profile rail without kinks. The arrangement of the grounding-pin sockets at a 45° angle allows unrestricted use of angular connectors.

---

# Features

Benefits	Practical, universal fastening Flexibility saves on warehousing In the 482.6 mm (19") section there is adequate space to route the infeed between the socket strip and the profile rail without kinks
Material	Aluminum section, natural anodized Socket inserts: Polycarbonate
Supply includes	Socket strip 2 mounting brackets Assembly components Integrated micro-fuse 5 x 20 mm (10 A) Without connection cables, must be provided by customer
Version	With IEC 320 input
Outlets	9 x Non-Heating Apparatus Socket C13
Dimensions	Height: 44 mm Depth: 44 mm Length: 482.6 mm Height: 1.73 " Depth: 1.73 " Length: 19 "
Length of connection cable	2 m 78.7 "
Connection cable (type)	H05VV-F3G1.5
Mounting dimensions	452.5 mm 17.8 "
Mounting dimension tolerance	25 mm 0.98 "
Rated operating voltage	250 V AC, 50 Hz
Rated voltage	250 V AC, 50 Hz
Rated current (max.)	10 A
Type of connection (electrical)	IEC 60320: C14

# Features

---

Installation options	Components with a 25 mm pitch pattern IT wall-mounted distributor, at the rear, horizontal (adequate width provided) Enclosure frame 482.6 mm (19") level
Note	Depending on the application, it is advisable to keep some load current in reserve to prevent nuisance tripping as a result of peak inrush currents The mounting distance is variable across a range of 25 mm, the distance specified is the center - center distance of the holes in the mounting brackets
Standards	Sockets: DIN VDE 0620-1
Socket color	Black
Packaging unit	1 pc(s).
Net weight	0.54 kg
Gross weight	0.61 kg
Customs tariff number	85366990
ETIM 9	EC000330
ECLASS 8.0	27142604
Product description	DK Socket strip, IEC 320 socket C13, 9-way, 250 V, 10 A, LHD: 482,6x44x44 mm, For IEC 320 connectors with IEC 320 input

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------