

Rittal – The System.

Faster – better – everywhere.



DK 7240.300

Socket strip

State: 3/5/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7240.300 - Socket strip with ammeter

To measure the power consumption of connected equipment, pin patterns: "ground contacts", variable mounting options.

Features

Model No.	DK 7240.300
Product description	The outlet strip with ammeter measures the power consumption of the connected consumers. The 482.6 mm (19") long outlet strip can optionally be mounted on the 19" mounting frame, on the housing frame or at the rear of the wall-mounted distributor. The installation bracket can be mounted in four different positions, allowing for variable mounting. The outlet strip can be used on any profile with 25 mm hole pattern, no additional mounting accessories are required.
Material	Aluminum section, natural anodized Socket inserts: Polycarbonate
Supply includes	Socket strip Two installation brackets Fasteners With 3 m connection cable (wire end ferrules)
Version	With ammeter
Outlets	7 x D, ground contact (type F, CEE 7/4)
Dimensions	Height: 45 mm Depth: 50 mm Length: 482.6 mm Height: 1.77 " Depth: 1.97 " Length: 19 "
Length of connection cable	3 m 118 "
Mounting dimensions	464.1 mm 18.3 "
Rated operating voltage	230 V AC, 50 Hz

Features

Rated voltage	230 V AC, 50 Hz
Rated current (max.)	16 A
Installation options	Components with a 25 mm pitch pattern Enclosure frame IT wall-mounted distributor, at the rear, horizontal (adequate width provided) 482.6 mm (19") level
Socket color	Gray
Packaging unit	1 pc(s).
Net weight	0.859 kg
Gross weight	1.18 kg
Customs tariff number	85366990
ECLASS 8.0	27142604

Approvals

Explanations	Declaration of conformity
--------------	---------------------------