Rittal – The System.

Faster – better – everywhere.



DK 7246.400

Adapter, 3 U

State: 11/15/2026 (Source: www.rittal.com/us-en)

DK 7246.400 - Adapter, 3 U Depth offset 100 mm

Used to recess the 482.6 mm (19") mounting of equipment inside enclosures with a 19" installation in the foremost position, such as server or electronic enclosures.



Features

Model No.	DK 7246.400
Product description	The adapter provides recessed mounting of equipment within the 19" rail. This ensures there is enough space in front of the equipment to integrate patch panels or switches, while utilizing the enclosure depth to the maximum.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Height units	3 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19" Installation depth for components: 19 ˝ Installation width for components: 19"
Packaging unit	2 pc(s).
Net weight	0.34 kg
Gross weight	0.37 kg
PCF/VE (cradle-to-gate)	1.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

Customs tariff number	83024900
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK Adaptor 482,6 mm (19"), 3 U, Depth offset 100 mm