

**Rittal – The System.**

Faster – better – everywhere.



**DK 5501.655**

**Component Shelf, Static Installation**

State: 6/18/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.655 - Component Shelf, Static Installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 19" mounting levels.

## Features

Model No.	DK 5501.655
Benefits	Tool-free, time-saving one-person assembly
Applications	Depth-variable to adapt to individual distances between levels
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear
Applications	For larger spacing between levels, it is necessary to reduce the pre-mounted spacing between levels; load capacity 50 kg.
Load capacity	50 kg
Dimensions	Width: 484 mm Width: 19.1 "
Suitable for	Enclosure type: VX IT TS IT TE TX CableNet
Distance between levels	400 - 600 mm 15.7 - 23.6 "
Packaging unit	1 pc(s).
Net weight	4.5 kg
Gross weight	4.82 kg
PCF/VE (cradle-to-gate)	25 kg CO2 eq (Cat B)

# Features

---

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Component shelf, WxH: 484 mm x 0,5 U, 50 kg, distance between levels: 400-600 mm, depth-variable, RAL 9005

---