

Rittal – The System.

Faster – better – everywhere.



DK 5501.655

Component Shelf, Static Installation

State: 10/3/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.655 - Component Shelf, Static Installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 19" mounting levels.

Features

Model No.	DK 5501.655
Benefits	Tool-free, time-saving one-person assembly
Applications	Depth-variable to adapt to individual distances between levels
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear
Applications	For larger distances between levels, you will need to reduce the preconfigured distance, load capacity 50 kg.
Load capacity	50 kg
Dimensions	Width: 484 mm Width: 19.1 "
Suitable for	Enclosure type: VX IT TS IT TE TX CableNet
Distance between levels	400 - 600 mm 15.7 - 23.6 "
Packaging unit	1 pc(s).
Net weight	4.5
Gross weight	4.82
PCF/VE (cradle-to-gate)	25 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177679092
E-Number Sweden	E7239587
ETIM 9	EC002620
ECLASS 8.0	27189261