

**Rittal – The System.**

Faster – better – everywhere.



**DK 7470.535**

**Fiber-optic splicing box with  
telescopic pull-out**

State: 6/19/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7470.535 - Fiber-optic splicing box with telescopic pull-out lockable

To accommodate splicing cassettes, telescopic pull-out provides easy access.

## Features

Model No.	DK 7470.535
Product description	The 482.6 mm (19") splicing box is used to hold splicing cassettes and can be installed in any network distributor within the 482.6 mm (19") rail and can be used as a fiberoptic end closure or distributor. The rear part of the splicing box is left completely open for cable routing, with a rubber clamping profile that provides protection from the ingress of dust. The fiber optic cables can be secured using cable ties or cable clamps, two strain relief clamps and the cable routing clips for the fiber dispenser provide a system-compatible solution for all fiber optic cabling.
Benefits	Telescopic pull-out provides easy access to the splicing cassettes and the cable clamping The variable cassette accommodates the twist-proof installation of all standard splicing cassettes The security lock on the front provides protection from unauthorized access
Material	Carbon steel
Color	RAL 7035
Supply includes	Splicing box Cable routing clips Security lock Box type plug-in unit cover Mounting accessories for patch panel
Number of splicing cassettes max	4
Note	Supplied without patch panels and splicing cassettes
Installation depth	363 mm 14.3 "
Height units	2 U

# Features

---

Packaging unit	1 pc(s).
Net weight	6.414 kg
Gross weight	6.752 kg
Customs tariff number	94039910
ETIM 9	EC001129
ECLASS 8.0	19170113
Product description	DK Fibre-optic splicing box