Rittal – The System.

Faster – better – everywhere.



DK 5501.705
Component Shelf, Static Installation

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 5501.705 - Component Shelf, Static Installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 19" mounting levels.





Features

Model No.	DK 5501.705
Benefits	Tool-free, time-saving one-person assembly
Applications	Depth-variable to adapt to individual distances between levels
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear
Load capacity	100 kg
Dimensions	Width: 484 mm Width: 19.1 ″
Suitable for	Enclosure type: VX IT TS IT TE
Distance between levels	600 - 900 mm 23.6 - 35.4 ″
Height units	1 U

© Rittal 2026

Features

Packaging unit	1 pc(s).
Net weight	7.6 kg
Gross weight	8.49 kg
PCF/VE (cradle-to-gate)	32.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Component shelf, WxH: 484 mm x 1 U, 100 kg, distance between levels: 600-900 mm, depth-variable, RAL 9005