## Rittal – The System.

Faster – better – everywhere.





# DK 5502.120 Cable route

State: 11/19/2025 (Source: rittal.com/us-en)



## DK 5502.120 - Cable route for TS

For cable clamping and routing for network and server applications.







#### **Features**

DK 5502.120
Easy mounting with tool-free quick-release fastening
Alternatively suitable for screw-fastening
Unique hole profle to acccomodate various cable management
accessories
For cable clamping and routing with network and server
applications
Carbon steel
RAL 9005
Mounting across the entire depth with 800 mm width, with 600 mm
width mounting only behind the second 19" level
Width: 115 mm
Width: 4.53 "
2,000: 2,200 mm
78.7: 86.6 <i>"</i>
1 pc(s).

© Rittal 2025

### **Features**

Net weight	3.6
Gross weight	3.88
Customs tariff number	85389099
EAN	4028177679306
E-Number Sweden	E7239778
ETIM 9	EC000012
ECLASS 8.0	27400703

© Rittal 2025 3