

Rittal – The System.

Faster – better – everywhere.



DK 5502.120

Cable route

State: 2/1/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



DK 5502.120 - Cable route for TS

For cable clamping and routing for network and server applications.



Features

Model No.	DK 5502.120
Benefits	Easy mounting with tool-free quick-release fastening Alternatively suitable for screw-fastening Unique hole profile to accommodate various cable management accessories
Applications	For cable clamping and routing with network and server applications
Material	Carbon steel
Color	RAL 9005
Note	Mounting across the entire depth with 800 mm width, with 600 mm width mounting only behind the second 19" level
Dimensions	Width: 115 mm Width: 4.53 "
Length	2,000: 2,200 mm 78.7: 86.6 "
Packaging unit	1 pc(s).

Features

Net weight	3.6
Gross weight	3.88
Customs tariff number	85389099
EAN	4028177679306
E-Number Sweden	E7239778
ETIM 9	EC000012
ECLASS 8.0	27400703
