

Rittal – The System.

Faster – better – everywhere.



DK 5502.550

Gland plate

State: 2/1/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.550 - Gland plate for VX IT, TS IT, TX CableNet

Potential equalization via assembly components and grounding points are available . The base plate is set to cover the entire base opening.

Features

Model No.	DK 5502.550
Version	Base plate, solid, with sliding panel, multi-piece
Product description	Equipotential bonding is provided via fastening components and grounding points. Base Plate Kit: To conceal the entire base opening. Base plate modules: Select modules in keeping with the application.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for	Enclosure type: TS IT TX CableNet Width: 800 mm Depth: 1,000 mm Enclosure type: TS IT TX CableNet Width: 31.5 " Depth: 39.4 "
Packaging unit	1 pc(s).
Net weight	7.94
Gross weight	8.42
PCF/VE (cradle-to-gate)	32.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177682498
E-Number Sweden	E7239575

Features

ETIM 9 EC002620

ECLASS 8.0 27189261